


# HPV-XL Polymer Seam Plates



## Overview

Versico's HPV-XL Polymer Seam Plates are used in conjunction with HPV-XL Fasteners for excellent back-out resistance and enhanced wind uplift ratings (Contact Versico for specifics regarding these ratings). The 16-barb profile on the underside of the plate reduces lateral movement when subjected to dynamic membrane loading.

## Features and Benefits

- Incorporates an oversized diameter hole to accommodate the larger wire size of the HPV-XL Fastener
- Increased slip resistance of membrane during uplift conditions
- Enhanced wind uplift ratings
- Locking plate prevents fastener backout
- No special tools required

## Installation

1. Position HPV-XL Polymer Seam Plates with barbs facing downward.
2. Secure HPV-XL Polymer Seam Plates using HPV-XL fasteners. Tighten fastener until fastener head "snaps" into plate recess.

REVIEW CURRENT VERSICO SPECIFICATIONS AND DETAILS FOR SPECIFIC INSTALLATION REQUIREMENTS.

## Precautions

- Eye protection is recommended during drilling and installation of fasteners.
- Cannot be directly installed over hard surfaces such as wood, concrete, brick, concrete block, DensDeck® or SECUROCK®.
- Use care to avoid over-torquing the fastener. Fastener must be tight enough so that the plate doesn't turn.

## Typical Properties and Characteristics

Size	2 3/8" Diameter (60mm)
Weight/Carton	26 lbs. (12 kg)
Quantity	1,000/carton
Pull Through Resistance	985 lbs. (447 kg)
Compatibility	Accepts Versico HPV-XL Fasteners

Typical properties and characteristics are based on samples tested and are not guaranteed for all samples of this product. This data and information is intended as a guide and does not reflect the specification range for any particular property of this product.



A SINGLE SOURCE FOR SINGLE-PLY ROOFING

800.992.7663 • [www.versico.com](http://www.versico.com)